

# ARROW®



## Multi-Lumen Central Venous Catheterization Set with Blue FlexTip® Catheter

REF **CV-15703-BZ** | 7 Fr. | 3 Lumen | 20 cm catheter length | **.032** inch dia. spring-wire guide

**Contents:**

- 1: Multi-Lumen Indwelling Catheter: 7 Fr. x 20 cm Radiopaque Polyurethane with Blue FlexTip®, Extension Line Clamps
- 1: Spring-Wire Guide, Marked: .032" (0.81 mm) dia. x 23-5/8" (60 cm) (Straight Soft Tip on One End - "J" Tip on Other) with Arrow Advancer with ECG Mark
- 1: Introducer Needle: 18 Ga. x 2-1/2" (6.35 cm) XTW
- 1: Syringe: 5 mL Luer-Slip
- 1: Tissue Dilator: 8.5 Fr. (2.8 mm) x 10.2 cm
- 3: Dust Cap: Non-Vented
- 1: SecondSite™ Adjustable Hub: Fastener
- 1: SecondSite™ Adjustable Hub: Catheter Clamp

- pt** Conjunto de Cateterização Venosa Central com Lúmen Múltiplo e Cateter Blue FlexTip
- es** Conjunto de cateterización venosa central de luz múltiple con catéter Blue FlexTip


All components are CE 0086 unless otherwise noted.

Rx only. **Warning: Read all package insert warnings, cautions and instructions prior to use. Failure to do so may result in severe patient injury or death.**

**California Prop. 65**

**Warning: Cancer and Reproductive Harm** [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov).

Fluid path components are non-pyrogenic.



Lumen	Priming Volume* (mL)	Flow Rate† (mL/hr)
Distal (16 Ga.)	0.47	3200
Medial (18 Ga.)	0.40	1500
Proximal (18 Ga.)	0.42	1600

\* Priming volumes are approximate and are done without accessories.  
† Based on 100 cm head height.

Catheter Cross Section

**EC REP** Teleflex Medical  
IDA Business and Technology Park  
Dublin Road, Athlone  
Co. Westmeath, Ireland  
**CE 0086**

**Manufacturer:**  
Arrow International, Inc.  
Subsidiary of Teleflex Incorporated  
2400 Bernville Road  
Reading, PA 19605 USA

**Teleflex®**  
[www.teleflex.com](http://www.teleflex.com)

IV-15703-140B (11/19)



## Multi-Lumen Central Venous Catheterization Set with Blue FlexTip® Catheter

REF **CV-15703-BZ**

7 Fr. | 3 Lumen | 20 cm catheter length | **.032** inch dia. spring-wire guide

# ARROW®