



REF CV-42703

ARROW®

7 Fr. 3 Lumen

16 cm catheter length

.032 inch dia. spring-wire guide

Arrowg+ard Blue Plus® Three-Lumen CVC

Contents:

- 1: Arrowg+ard Blue Plus®¹ Three-Lumen Catheter: 7 Fr. (2.5 mm OD) x 16 cm
- 1: Spring-Wire Guide, Marked: .032" (0.81 mm) dia. x 17-3/4" (45 cm) (Straight Soft Tip on One End - "J" Tip on Other) with Arrow Advancer
- 1: Introducer Needle: 18 Ga. x 2-1/2" (6.35 cm) XTW
- 1: Syringe: 5 mL Luer-Slip
- 1: Tissue Dilator: 8.5 Fr. (2.8 mm) x 10.2 cm
- 3: Dust Cap: Non-Vented
- 1: SecondSite™ Adjustable Hub: Fastener
- 1: SecondSite™ Adjustable Hub: Catheter Clamp

¹Licensed under US Patent No. 7,329,412.

All components are CE 2797 unless otherwise noted.

Warning: Read all package insert warnings, precautions, and instructions prior to use. Failure to do so may result in severe patient injury or death. www.teleflex.com/IFU

Not made with natural rubber latex.

Store below 25°C (77°F). Avoid excessive heat above 40°C (104°F). Fluid path components are non-pyrogenic.

Contraindications: The Arrowg+ard Blue Plus antimicrobial catheter is contraindicated for patients with known hypersensitivity to chlorhexidine, silver sulfadiazine and/or sulfa drugs.



CAS # 7440-48-4



Lumen

Priming Volume* (mL)

Gravity Flow Rate† (mL/hr)

| | | |
|-------------------|------|------|
| Distal (16 Ga.) | 0.38 | 2490 |
| Medial (18 Ga.) | 0.37 | 1162 |
| Proximal (18 Ga.) | 0.39 | 1328 |

* Priming volumes are approximate and are done without accessories.

† Flow rate values are approximate and are determined using deionized water at 100 cm head height.



EU Authorized Representative and Importer:

EC REP

CE

2797

Teleflex Medical
IDA Business and
Technology Park
Dublin Road, Athlone
Co. Westmeath, Ireland



Arrow International LLC
Subsidiary of Teleflex Incorporated
3015 Carrington Mill Blvd.
Morrisville, NC 27560 USA

Teleflex®
www.teleflex.com

LBL051207 R03 (2023-12)

LOT



7 Fr. 3 Lumen

16 cm catheter length

.032 inch dia. spring-wire guide

REF CV-42703

Arrowg+ard Blue Plus® Three-Lumen CVC

ARROW®