



REF EU-12802-N

(IPNXXXXXX)

8 Fr. 2 Lumen

16 cm catheter length












.032 inch dia. spring-wire guide


Two-Lumen CVC

Contents:

- 1: Two-Lumen Catheter: 8 Fr. (2.8 mm OD) x 16 cm
 - 1: Spring-Wire Guide, Nitinol, Marked: .032" (0.81 mm) dia. x 17-3/4" (45 cm) (Straight Soft Tip on One End - "J" Tip on Other) with Arrow Advancer
 - 1: Introducer Needle: 18 Ga. x 2-1/2" (6.35 cm) XTW
 - 1: Syringe: 5 mL Luer-Slip
 - 1: Tissue Dilator: 9 Fr. (3.0 mm) x 10.2 cm
 - 1: SecondSite™ Adjustable Hub: Fastener
 - 1: SecondSite™ Adjustable Hub: Catheter Clamp
- All components are CE 2797 unless otherwise noted.

Warning: Read all package insert warnings, precautions, and instructions prior to use. Failure to do so may result in severe patient injury or death. www.teleflex.com/IFU
Not made with natural rubber latex.
Fluid path components are non-pyrogenic.



CAS # 7440-48-4

en

be

bg

hr

cs

da

nl

et

fi

fr

de

el

hu

is

it

lv

lt

no

pl

pt

ro

ru

sr

sk


sl

es

sv

tr

uk


 Lumen	Priming Volume* (mL)	Gravity Flow Rate† (mL/hr)
Distal (14 Ga.)	0.66	5279
Proximal (14 Ga.)	0.71	4764

* Priming volumes are approximate and are done without accessories.
† Flow rate values are approximate and are determined using deionized water at 100 cm head height.

 EU Authorized Representative and Importer:

 Teleflex Medical
IDA Business and
Technology Park
Dublin Road, Athlone
Co. Westmeath, Ireland


All components are CE 2797 unless otherwise noted.

 Arrow International LLC
Subsidiary of Teleflex Incorporated
3015 Carrington Mill Blvd.
Morrisville, NC 27560 USA

Product of xxx
Packaged in xxx

LOT LotNumber

 YYYY-MM-DD

 YYYY-MM-DD



(01)XXXXXXXXXXXXXX
(17)YYMMDD
(11)YYMMDD
(10)LotNumber

Teleflex®
www.teleflex.com

LBL054310 R02 (2024-08)



8 Fr. 2 Lumen

16 cm catheter length

.032 inch dia. spring-wire guide

REF EU-12802-N

Two-Lumen CVC

