

Dimensions:
 Width: 6-9/64" (15.6 cm)
 Length: 8-21/32" (22 cm)

PB-50014-100B
PBZ-50014-103A

T50014100A6 Dimensions: 5 7/8" x 7 5/8"

ARROW



REF CV-15703-E (IPNXXXXXX)

Three-Lumen CVC

Contents:


- 1: Three-Lumen Catheter: 7 Fr. (2.5 mm OD) x 20 cm
- 1: Spring-Wire Guide, Marked: .032" (0.81 mm) dia. x 23-5/8" (60 cm) (Straight Soft Tip on One End - "J" Tip on Other) with Arrow Advancer
- 1: Introducer Needle: 18 Ga. x 2-1/2" (6.35 cm) XTW
- 1: Pressure Transduction Probe
- 1: Arrow® Raulerson Spring-Wire Introduction Syringe: 5 mL
- 1: Tissue Dilator: 8.5 Fr. (2.8 mm) x 10.2 cm
- 3: Dust Cap: Non-Vented
- 1: SecondSite™ Adjustable Hub: Fastener
- 1: SecondSite™ Adjustable Hub: Catheter Clamp

All components are CE 2797 unless otherwise noted.

Rx only Warning: Read all package insert warnings, precautions, and instructions prior to use. Failure to do so may result in severe patient injury or death. www.teleflex.com/IFU California Prop. 65

⚠ WARNING: Cancer and Reproductive Harm.
www.P65Warnings.ca.gov

Not made with natural rubber latex. Fluid path components are non-pyrogenic.



CAS # 7440-48-4

EU Authorized Representative and Importer:

EC REP Teleflex Medical
 IDA Business and
CE Technology Park
 2797 Dublin Road, Athlone
 Co. Westmeath, Ireland

All components are CE 2797 unless otherwise noted.

Arrow International LLC
 Subsidiary of Teleflex Incorporated
 3015 Carrington Mill Blvd.
 Morrisville, NC 27560 USA

Product of xxx
 Packaged in xxx

Teleflex
www.teleflex.com



Lumen	Priming Volume* (mL)	Gravity Flow Rate† (mL/hr)
Distal (16 Ga.)	0.47	2656
Medial (18 Ga.)	0.40	1245
Proximal (18 Ga.)	0.42	1328

* Priming volumes are approximate and are done without accessories.
 † Flow rate values are approximate and are determined using deionized water at 100 cm head height.

LOT LotNumber

YYYY-MM-DD

YYYY-MM-DD



(01)XXXXXXXXXXXXXXXXXX
 (17)YYMMDD
 (11)YYMMDD
 (10)LotNumber

LBL055590 R02 (2024-05)



7 Fr. **3** Lumen **20** cm catheter length **.032** inch dia. spring-wire guide

REF CV-15703-E

Three-Lumen CVC

ARROW