



REF **BR-12854** (IPNXXXXXX)

8.5 Fr. **4** Lumen **16** cm catheter length **.032** inch dia. spring-wire guide

Four-Lumen CVC

Contents:

- 1: Four-Lumen Catheter: 8.5 Fr. (3.0 mm OD) x 16 cm
- 1: Spring-Wire Guide, Marked: .032" (0.81 mm) dia. x 23-5/8" (60 cm) (Straight Soft Tip on One End - "J" Tip on Other) with Arrow Advancer
- 1: Catheter: 18 Ga. x 2-1/2" (6.35 cm) Radiopaque over 20 Ga. RW Introducer Needle
- 1: Introducer Needle: 18 Ga. x 2-1/2" (6.35 cm) XTW
- 1: Syringe: 5 mL Luer-Slip
- 1: Tissue Dilator: 9 Fr. (3.0 mm) x 10.2 cm
- 4: Dust Cap: Non-Vented
- 1: SecondSite™ Adjustable Hub: Fastener
- 1: SecondSite™ Adjustable Hub: Catheter Clamp
- 1: Scalpel: #11
- 4: Stopcock: 4-way High-Flow

Warning: Read all package insert warnings, precautions, and instructions prior to use. Failure to do so may result in severe patient injury or death. www.teleflex.com/IFU
Not made with natural rubber latex.
 Fluid path components are non-pyrogenic.

All components are CE 2797 unless otherwise noted.



CAS # 7440-48-4

en be bg hr cs da nl et fi fr de el hu is it lv lt no
 pl pt ro ru sr sk sl es sv tr uk



Lumen	Priming Volume* (mL)	Gravity Flow Rate† (mL/hr)
Distal (16 Ga.)	0.50	2756
Medial 1 (14 Ga.)	0.60	5038
Medial 2 (18 Ga.)	0.40	1386
Proximal (18 Ga.)	0.40	1511

* Priming volumes are approximate and are done without accessories.

† Flow rate values are approximate and are determined using deionized water at 100 cm head height.

EU Authorized Representative and Importer:

Teleflex Medical
 IDA Business and
 Technology Park
 Dublin Road, Athlone
 Co. Westmeath, Ireland
 2797

All components are CE 2797 unless otherwise noted.

Arrow International LLC
 Subsidiary of Teleflex Incorporated
 3015 Carrington Mill Blvd.
 Morrisville, NC 27560 USA

Product of xxx
 Packaged in xxx

LOT Lot Number

YYYY-MM-DD

YYYY-MM-DD



(01)XXXXXXXXXXXXXXXXXX
 (17)YYMMDD
 (11)YYMMDD
 (10)Lot Number

Teleflex®
www.teleflex.com

LBL055691 R02 (2025-04)



8.5 Fr. **4** Lumen **16** cm catheter length **.032** inch dia. spring-wire guide

REF BR-12854

Four-Lumen CVC

