



REF CS-12854-E

(IPNXXXXXX)

8.5 Fr. 4 Lumen

16 cm catheter length

.032 inch dia. spring-wire guide

Four-Lumen CVC

Contents:

- 1: Four-Lumen Catheter: 8.5 Fr. (3.0 mm OD) x 16 cm
- 1: Spring-Wire Guide, Marked: .032" (0.81 mm) dia. x 23-5/8" (60 cm) (Straight Soft Tip on One End - "J" Tip on Other) with Arrow Advancer with ECG Mark
- 1: Catheter: 18 Ga. x 2-1/2" (6.35 cm) Radiopaque over 20 Ga. RW Introducer Needle
- 1: Introducer Needle: 18 Ga. x 2-1/2" (6.35 cm) XTW
- 1: Pressure Transduction Probe
- 1: Syringe: 5 mL Luer-Slip
- 1: Arrow® Raulerson Spring-Wire Introduction Syringe: 5 mL
- 1: Tissue Dilator: 9 Fr. (3.0 mm) x 10.2 cm
- 4: Dust Cap: Non-Vented
- 1: SecondSite™ Adjustable Hub: Fastener
- 1: SecondSite™ Adjustable Hub: Catheter Clamp

All components are CE 2797 unless otherwise noted.

Warning: Read all package insert warnings, precautions, and instructions prior to use. Failure to do so may result in severe patient injury or death. www.teleflex.com/IFU
Not made with natural rubber latex.
Fluid path components are non-pyrogenic.



CAS # 7440-48-4

en be bg hr cs da nl et fi fr de el hu is it lv lt no
pl pt ro ru sr sk sl es sv tr uk

Lumen	Priming Volume* (mL)	Gravity Flow Rate† (mL/hr)
Distal (16 Ga.)	0.50	2756
Medial 1 (14 Ga.)	0.60	5038
Medial 2 (18 Ga.)	0.40	1386
Proximal (18 Ga.)	0.40	1511

* Priming volumes are approximate and are done without accessories.

† Flow rate values are approximate and are determined using deionized water at 100 cm head height.



EU Authorized Representative and Importer:



Teleflex Medical
IDA Business and
Technology Park
Dublin Road, Athlone
Co. Westmeath, Ireland



All components are CE 2797 unless otherwise noted.



Arrow International LLC
Subsidiary of Teleflex Incorporated
3015 Carrington Mill Blvd.
Morrisville, NC 27560 USA

Product of xxx
Packaged in xxx

LOT Lot Number



YYYY-MM-DD



YYYY-MM-DD



(01)XXXXXXXXXXXXXX
(17)YYMMDD
(11)YYMMDD
(10)Lot Number

Teleflex®
www.teleflex.com

LBL055958 R03 (2025-01)



8.5 Fr. 4 Lumen

16 cm catheter length

.032 inch dia. spring-wire guide

REF CS-12854-E

Four-Lumen CVC

