

Dimensions: 6" (15,2 cm) x 8-1/2" (21,6 cm)

T50014100A6 Dimensions: 5 7/8" x 7 5/8"

PB-50014-001B

PBZ-50014-001A

ARROW®



REF CS-15703

(IPNXXXXXX)

Three-Lumen CVC

Contents:



- 1: Three-Lumen Catheter: 7 Fr. (2.5 mm OD) x 20 cm
- 1: Spring-Wire Guide, Marked: .032" (0.81 mm) dia. x 23-5/8" (60 cm) (Straight Soft Tip on One End - "J" Tip on Other) with Arrow Advancer with ECG Mark
- 1: Catheter: 18 Ga. x 2-1/2" (6.35 cm) Radiopaque over 20 Ga. RW Introducer Needle
- 1: Introducer Needle: 18 Ga. x 2-1/2" (6.35 cm) XTW
- 1: Syringe: 5 mL Luer-Slip
- 1: Tissue Dilator: 8.5 Fr. (2.8 mm) x 10.2 cm
- 3: Dust Cap: Non-Vented
- 1: SecondSite™ Adjustable Hub: Fastener
- 1: SecondSite™ Adjustable Hub: Catheter Clamp

All components are CE 2797 unless otherwise noted.

Rx only Warning: Read all package insert warnings, precautions, and instructions prior to use. Failure to do so may result in severe patient injury or death. www.teleflex.com/IFU California Prop. 65

⚠ **WARNING:** Cancer and Reproductive Harm.
www.P65Warnings.ca.gov

Not made with natural rubber latex. Fluid path components are non-pyrogenic.



Lumen

Priming
Volume*
(mL)

Gravity
Flow
Rate†
(mL/hr)

Distal (16 Ga.)	0.47	2656
Medial (18 Ga.)	0.40	1245
Proximal (18 Ga.)	0.42	1328

* Priming volumes are approximate and are done without accessories.

† Flow rate values are approximate and are determined using deionized water at 100 cm head height.



CAS # 7440-48-4



EU Authorized
Representative and
Importer:

EC REP



Teleflex Medical
IDA Business and
Technology Park
Dublin Road, Athlone
Co. Westmeath, Ireland
2797

All components are CE 2797
unless otherwise noted.



Arrow International LLC
Subsidiary of Teleflex Incorporated
3015 Carrington Mill Blvd.
Morrisville, NC 27560 USA

Product of xxx
Packaged in xxx

Teleflex®
www.teleflex.com

LOT

Lot Number



YYYY-MM-DD



YYYY-MM-DD



(01)XXXXXXXXXXXXXX
(17)YYMMDD
(11)YYMMDD
(10)Lot Number

LBL076552 R00 (2025-07)



7 Fr. 3 Lumen

20 cm catheter length

.032 inch dia. spring-wire guide

REF CS-15703

Three-Lumen CVC

ARROW®